

1.T1

Shim mode	Tune up	
Adjust with body coil	On	
Confirm freq. adjustment	Off	
Assume Silicone	Off	
? Ref. amplitude 1H	0.000 V	
Adjustment Tolerance	Auto	
Adjust volume		
Position	Isocenter	T1
Orientation	Transversal	
Rotation	0.00 deg	
R >> L	350 mm	
A >> P	263 mm	
F >> H	350 mm	

2.DTI

Shim mode	Standard	
Adjust with body coil	Off	
Confirm freq. adjustment	Off	
Assume Silicone	Off	DTI
? Ref. amplitude 1H	0.000 V	
Adjustment Tolerance	Auto	
Adjust volume		
! Position	L0.0 A9.0 H6.6	
! Orientation	Transversal	
! Rotation	0.00 deg	
! R >> L	192 mm	
! A >> P	192 mm	
! F >> H	144 mm	